Krystal Klear Water

Water Filtration System &

Electronic DeScaler

Instruction & Owners Manual

WELCOME

INSTALLATION OVERVIEW BEFORE YOU START PROGRAMMING INSTRUCTIONS – FILTRATION SYSTEM INSTALL INSTRUCTIONS – ELECTRONIC DESCALER NEW SP4000 FITTINGS

FREQUENTLY ASKED QUESTIONS, HELPFUL HINTS

These are the components of this whole House Water Treatment equipment





C-SERIES

Time Clock Series Models

1" & 1-1/4" Control Valve

Time Clock Programming Guide




Front Cover and Drive Assemb/y

V3186-01

| Part No. | Description | Qty |
|------------|-----------------------------|-----|
| C3175TC-01 | IC Front Cover Asy | 1 |
| C3107-01 | Motor Asy | 1 |
| C3106-01 | Drive Bracket & Spring Clip | 1 |
| C3818TC | IC PC Board 4-Digit | 1 |
| C3110 | Drive Reducing Gear I2x363 | |
| C3109 | Drive Gear Cover | 1 |
| C3002TC | TCDriveAssemjy. | |
| Not Shown | | |
| C3186 | AC Adapter I2OV-12V 1 | |
| C3186EU | AC Adapter 220 240V 12VEU | |
| C3186UK | AC Adapter 220-240V- | |


WS1 AC Adapter Cord Only



Part Shown in picture C3175TC-01




Part shown in picture C3818TC



Part shown in picture C3107-01

Complete assembly part C3002



Parts shown in picture C3110, C3109, C3106-01

Drive Cap Assembly, Down flow Piston, Rçgenerant Piston & Spacer Stack Assembly

| Part No. | Description | Qty | |
|-----------|---|---------------|--|
| C3430 | Spacer Stack Assembly | 1 | |
| C3004 | Drive Cap ASY | 1 | |
| C3178 | Drive Back Plate | 1 | |
| C3407 | Piston Downfl ow ASY | 1 | |
| C3174 | Regenerant Piston | 1 | |
| C3135 | 0-ring 228 | 1 | |
| C3180 | 0-ring 337 | 1 | |
| C3358 | 0-ring 219 (Dist. Tube Opening | 3 1.32) 1 | |
| C3357: | 0-ring218(Dist. Tübé Openinq | | |
| Not Shown | | | |
| C3020 | Body ASY Downflow (Distributor Tube Op | pening 1.32") | |
| C3020-01 | 1.25 Mixing Valve Body Downflow Assy (Distributor Tube Opening 1.32') | | |
| C3020-02 | 1.25Body Assy Downflow (Distributor Tube Opening 32mm) | | |
| C3020-03 | 1.25 Mixing Valve Body Downflow Assy (Distributor Tube Opening 32mm) | | |

| Part No. | Description | Qty | |
|-------------|---------------------------------|-----|---|
| C3005 | 1 'Spacer Stack Assembly 1 | | |
| C3004 | Drive Cap Assembly | 1 | |
| C3178 | Drive Back Plate | | 1 |
| C3011 | Piston Downflow Assembly | | 1 |
| C3174 | Regenerant Piston | | 1 |
| C3135 | 0-ring 228 | 1 | |
| C3180 | 0-ring 337 | | 1 |
| C3105 | I 0-ring 215 (Distributer Tube) | 1 | |
| Not Charrie | | | |

Not Shown

C3001 Body ASYDownflow 1

C3001-02 I Mixing Valve Body ASY

1" Control Valve Part Numbers C3118

1-1/4' Control Valve Part Numbers

Applies to Both Size Control Valves


Words in the pictures: Black Plug Grey Plug, Grey Ring, Distributor, retainer, Grey Spacer Color , Black Plug

*Only for valves that have a 32mm Distributor Tube Opening

C-Series 1' & 1-1/4" Time Clock Manual

C-Series 1" & 1-114" Control Valve Identification

C-Series with 1.050" Distributor Tube Opening Identification



C-Series 1-1/4" with 1.32H Distributor Tube Opening Identification

Words in picture: Black Spacer Color, Grey Plug

C-Series 14/4" with 32mm Distributor Tube Opening Identification

Words in picture: Grey Plug, Grey Spacer Color, Grey Ring, Grey Distributor O-Ring Retainer

C-Series 1 & 1-1/4" Time Clock Manual

